INSULATING RUBBER GLOVES



Contact a Salisbury customer service representative for extensive arc flash testing data performed on the insulating rubber gloves.

■ SALISBURY INSULATING RUBBER GLOVES are available in sizes 7 through 12, including half sizes. Proper fit is important to minimize chafing and fatigue. To determine glove size, measure the circumference around the palm. Allow for additional room if fabric glove liners are to be worn, especially with thermal liners.

Class 00 are available in red and black, Type I Natural Rubber or blue and contrasting blue/orange Type II Salcor® ozone resistant rubber. Class 0 gloves are available in red, yellow and black, Type I Natural Rubber or blue Type II Salcor® ozone resistant rubber. The contrast between the thin outer orange color against the inner blue color makes inspecting for cuts and tears easier when the glove is inflated or stretched.

Class 2 glove are available in Type I Natural Rubber only. All insulating rubber gloves are extremely flexible and make working with small parts easy. The gloves meet or exceed ASTM D120 and IEC EN60903 Standards.



INSULATING RUBBER GLOVES MAXIMUM USAGE

	Proof Test	Max. Use
Class	Voltage AC / DC	Voltage AC / DC
00	2500 / 10,000	500 / 750
0	5,000 / 20,000	1,000 / 1,500
1	10,000 / 40,000	7,500 / 11,250
2	20,000 / 50,000	17,000 / 25,500
3	30,000 / 60,000	26,500 / 39,750
4	40,000 / 70,000	36,000 / 54,000



Measure the circumference around the palm to determine the size of the glove.

INSULATED RUBBER GLOVES

	Class	Length	Color	Size (choose one below)
E	00	11 or 14	R, BL, B	7, 8, 8H, 9, 9H
Е	0	11 or 14	R, BL, B, Y	10, 10H, 11, 12
Е	1	14,16 or 18	B, YB or RB	
E	2	14,16 or 18	B, YB or RB	

Class 3 and Class 4 Available.

EXAMPLE: E011R10 is a Class 0 11" red glove size 10.

Type I Natural Rubber available in: R=Red, Y=Yellow, B=Black, RB=Red in, Black out, YB=Yellow in, Black out

Type II Salcor® Rubber available in: BL=Blue



▼ TEN-FOUR® Glove Dust is a cooling, frictionless powder that absorbs moisture and perspiration when wearing rubber gloves. The 5-oz. bottle easily fits in a pocket or glove bag. The 4-quart bulk package is used in test labs as a dusting powder.

TEN-FOUR® GLOVE DUST

ILIT I OUIT	OLUTE DUST				
Cat. No.	Description	Weight			
		lbs. (kgs)			
10-4	12 @ 5 oz. squeeze bottles	5.5 (12)			
10-4-4QT	4 qt. bulk, single	8 (19)			